

HIGH SHEAR HOMOGENIZER FOR PHARMACEUTICAL APPLICATIONS

For Pilot/Small Production Scale Processing

New!

HMI

- Easier to use
- Data logging
- Access levels
- Larger screen

Enclosure

- Enclosed piping for in-process viewing and operator safety
- Small footprint with pharma grade casters and pads for mobility



The ShearJet HP1200 V2PH series electric-hydraulic processor runs sample sizes of 1L (options dependent) and up in distinct passes or continuous runs. Multiple samples may be processed in a short time span. This processor is specifically designed to meet the exacting requirements of the pharmaceutical industry by offering a Pharma and a more feature inclusive Pharma Premium version. Because the HP1200 V2 series is equipped with two multiplier pumps, it achieves near-continuous flow, subjecting formulations to identical processing conditions from start to finish. The HP1200V2PH is capable of operating from seconds for smaller samples to continuous for very large batches.

Performance:

- Our diamond Reaction Chamber® module with specially designed micro channels achieve consistent, uniform, repeatable results
- Long chamber life
- Integrated HMI with multi-level user interface allows the operator to monitor and program pressure, product temperature, volume processed, process duration, and alarms
- UL and CE compliance
- Data acquisition via USB or Ethernet

Easy-To-Clean:

- Low dead volume allows for easy cleaning

Economy:

- Save on raw material costs due to low dead volume
- Process samples in minutes
- Low maintenance cost
- Minimal seals and connections

























Specifications

Power: Electric-hydraulic 10 HP, 60 Hz, 230/460 VAC, 23.2/11.6 Amps; (50 Hz, 190/380 VAC, 27.8/13.9 Amps on request)
 Dimensions (WxLxH): 38.5 x 32.8 x 62.8
 Operating time: System can run from seconds to continuous

Shear Jet	HP1200-10PH	HP1200-20PH	HP1200-30PH
Minimum sample size* mL	1L (options dependent)	1L (options dependent)	1L (options dependent)
Pressure Kpsi (max.)	10	20	30
Pressure bar (max.)	690	1379	2068
Flow rate** L/min	3.5-3.8	1.5-1.8	1.0-1.2

*Based on Premium model, and dependent on options selection • **Dependent on Reaction Chamber module selection

Features

Features	Standard Model	Premium Model
Integrated sanitary feed pump		
Ceramic plunger		
CIP bypass for heat exchanger with diaphragm valves		
Flush diaphragm inline process pressure transducer		
Data Recorder enabling 21 CFR Part 11 compliance	option	
Touchscreen HMI with advanced features		
Diamond Reaction Chamber module and Back Pressure Reaction Chamber module		
2 RTDs		
3 RTDs		
Product outlet temperature control		
Product heat exchanger (tube and shell)		
Product heat exchanger (tube and shell, drainable)		
Product path EP & passivated		
Tools & Spares		
FAT/SAT		
IQ/OQ	option	

Dyhydromatics Corporate Headquarters

63 Great Road, Suite 103
 Maynard, MA 01754
 Phone +1 978 461 0200 • Fax: +1 978 461 0201
 Customer Service: (Option 4)
 info@dyhydromatics.com
 Sales: sales@dyhydromatics.com

Dyhydromatics European Head Office

Kelterstrasse 9, 75236 Kaempfelbach, Germany
 Customer Service Europe:
 Phone +49 7231 167 4048
 Sales: info-europe@dyhydromatics.com

Dyhydromatics, India

A-7, Mangal Society, Shreenagar
 Wagle Estate, Thane (W) - 400604, India
 Phone +91 77381 42553
 Email: info-india@dyhydromatics.com

FORCE BLUE is the only nonprofit organization in the world that provides "mission therapy" for former combat divers by retraining, retooling and deploying them

on missions of environmental conservation, preservation and restoration. We are pleased to support FORCE BLUE by donating a portion of proceeds from every new equipment sale.

